

TA Indoor power wheelchair request for quote



0800 238 523
sales@mortonperry.co.nz

For comparison charts & specifications visit:
mortonperry.co.nz

Client Name: _____ User weight: _____

Therapist: _____ Date: _____

Organisation: _____

Enable ACC Enable MOH Accessable MOH

Standard Specifications* - No up-charge

- Power functions: tilt, elevate
- Manual back recline 50 degrees
- Turning radius 18"/45cm
- Base width 22"/56cm / chair length w/o footrest 27"/69cm
- 10" Front wheels
- Super low floor to seatpan 12"/38cm with power elevate
- RNET expandable electronics
- 2 Pole, 450w motors, Range max 22km
- Controller Swinaway RH or LH
- The client can remain seated in the power wheelchair during vehicle transport. Safety crash tested design. ISO7179-19, NZ LVVTA 45-60 2.6.

Seat width & depth

Width

Junior

- 10"/25.4cm 18"/45.7cm
- 12"/30.5cm 20"/50.8cm
- 14"/35.6cm 21.5"/54.6cm
- 16"/40.6cm other _____

Depth

- 10"/25.4cm 18"/45.7cm
- 12"/30.5cm 20"/50.8cm
- 14"/35.6cm 21.5"/54.6cm
- 16"/40.6cm other _____

Power Functions - base

- At no charge: Tilt Elevate
- Back recline Power Centre

Floor to seat pan (F)

- 15-16.75" *Standard 19-19.75"
- 17-17.75" Other _____
- 18-18.75" _____

*With TA power elevate functions

Maximum overall width

- 22"/56cm Standard

TA Indoor



TA Junior



Lower leg support assembly

TA Indoor

- Manual - Centre
- Manual - 70° swing away - stepless L/H
- Manual - 70° swing away - stepless R/H

- Power Centre - standard (13"-18.5")
- Power Centre - short (10"-13.5")
- Power Centre - short (pivots under seat)
- Power Elevating - L/H
- Power Elevating - R/H

Junior

- Manual - Centre

Footplate

TA Indoor

- Manual centre - standard
- Manual centre - with pull up system
- Manual centre - wider with extended lip
- Divided left & right (pair)
- Electric flip-up
- Posterior foot support (heel loops)

Junior

- Manual centre - standard

Controller electronics

RNET is standard

- PG JSM LED w/o display (no lights) (standard on Indoor + Junior)
- PG JSM2 Large colour screen (can be used on chair fitted with LED lights)
- PG JSM2 Bluetooth Large colour screen
- PG JSM LED with lights (for chair fitted with LED lights)
- PG JSM Colour screen with lights (for chair fitted with LED lights)
- Attendant control dual - Standard
- Attendant control carer handle
- Head array

Back Configuration

- No upholstery
- Tall straight 1" - adjustable width (also for Junior)
- Contour design - adjustable width
- Contour design - adjustable width - Junior

Controller swing-away / dropdown

- Right hand side swingaway
- Left hand side swingaway
- Dropdown
- Swing-away

Stump support

- Left
- Right
- Both

Leg Support

- Drop in seat guides
- Thigh guides - Med (10x13cm)
- Thigh guides - Lrg

Arm support


- Desk
- Flip-up
- Adult
- Standard leather
- Full length
- Dual post flip-up
- Paediatric
- Gel
- Gutter

Pelvic positioning belt

- Standard
- Small
- 2-point padded
- Medium/Large
- 4-point padded

Tyres

- Drive tyres: Pneumatic (std)
- Solid



Min. Floor to seatpan height = Lower leg length - cushion + clearance or Seat to floor = C-E+G

Seating - Cushion

<input type="checkbox"/> Not required		Size (width x height):	Covers:
<input type="checkbox"/> Vicair Active O2	6cm	_____	
<input type="checkbox"/> Vicair Active O2	9cm	_____	Inco Comfair
<input type="checkbox"/> Vicair Adjuster O2	6cm	_____	<input type="checkbox"/> <input type="checkbox"/>
<input type="checkbox"/> Vicair Adjuster O2	10cm	_____	<input type="checkbox"/> <input type="checkbox"/>
<input type="checkbox"/> Vicair Adjuster O2	12cm	_____	<input type="checkbox"/> <input type="checkbox"/>
<input type="checkbox"/> Vicair Vector O2	6cm	_____	<input type="checkbox"/> <input type="checkbox"/>
<input type="checkbox"/> Vicair Vector O2	10cm	_____	<input type="checkbox"/> <input type="checkbox"/>
<input type="checkbox"/> Nxt Biofit	10cm	_____	<input type="checkbox"/> <input type="checkbox"/>
<input type="checkbox"/> Other (please specify)		_____	

VICAIR O2
ACTIVE 9




VICAIR O2
ADJUSTER 10



VICAIR O2
VECTOR 10



nxt
SEATING
Biofit



Seating - Back system

<input type="checkbox"/> Not required	Size (width x height):
<input type="checkbox"/> Nxt Xtend (AC)	_____
<input type="checkbox"/> Nxt Xtend Deep (PC)	_____
<input type="checkbox"/> Nxt Optima Carbon (AC)	_____
<input type="checkbox"/> Nxt Optima Carbon Deep (PC)	_____
<input type="checkbox"/> Other (please specify)	_____

nxt
SEATING
Xtend




nxt
SEATING
Optima Carbon



Headrest

<input type="checkbox"/> Not required	
<input type="checkbox"/> TA standard headrest (leather)	<input type="checkbox"/> TA Junior 5"
<input type="checkbox"/> Nxt Multifit - Contoured	<input type="checkbox"/> TA Junior 7"
<input type="checkbox"/> Nxt Multifit - Large	
<input type="checkbox"/> Nxt Multifit - Extra Large	
<input type="checkbox"/> Other (please specify) _____	

Includes headrest stem & brackets to attach to back system.



Set-up Instructions

Accessories (view accessories catalogue on our website)